

**(2) Copeland Water Cooled Condensing Units on Skid - 10 Ton**

**Mfg: Copeland**

**Model: W3DD-0503-TFD-001**

**Stock No: SNBB339.0**

**Serial No:**

(2) Copeland Water Cooled Condensing Units on Skid. Model: W3DD-0503-TFD-001. Design pressure: high side 350 psig. / low side 162 psig. Nominal capacity: 64,900 Btuh or 5.41 tons with R-22 at a 105°F condensing temperature and a 40°F suction temperature. Water flow rate: 7.8 gpm at 2.4 psi. Water inlet temperature: 85°F. (2) Copeland Discus semi-hermetic compressors. Model: 2DC3-0500-TFD-100, S/N's: ET 98A058020S and ET 98A05755S. Electrical requirements: 380-420/460 V, 10.4 RLA, 60.0 LRA, 50/60 Hz, 3 phase. Inlets/outlets: (2) 1/2 in. dia. pipes, (4) 1 in. dia. pipes, (1) 1-1/4 in. dia. pipe, (2) 1-1/2 in. dia. pipes. Overall dimensions: 5 ft. L x 4 ft. W x 5 ft. 4 in. H. (ACN125a).







