

Buffalo Grinder/Extruder

Mfg: Buffalo

Model: 78BG

Stock No. SSLP081.3

Serial No. 2520X

Buffalo Grinder/Extruder. Model: 78 BG. S/N: 2520X. General Electric motor, 10 hp, 1160 & 960 rpm, 230 & 460 V, 23.00/13.8 & 30/15.3 amps, 60 Hz, 60 & 50 cycles. Top stainless steel pan: 86 in. L x 40 in. W x 6 in. H.; inlet: 2-1/2 in. with (21) holes. Screw dimensions: 6 in. diameter x 30 in. L. (3) Product outlet discs: 8-1/2 in. diameter. Disc opening diameter: disc #1: 1 in., #2: 3/4 in., #3: 3/8 in. Overall dimensions: 96 in. L x 80 in. W x 66 in. H.



