

Stainless Steel Dual Fan Evaporator Unit- 5.8 Ton

Mfg:

Model:

Stock No. SSLP347.3

Serial No.:

Stainless Steel Dual Fan Evaporator Unit- 5.8 Ton. (2) Motors. Motor #1- Century Motor, 1/2 hp, 1140 rpm, 208-230/460 V, 2.0-1.9/0.95 amps, 60 Hz, 3 phase. Motor #2- Franklin motor, 1/2 hp, 1140/950 rpm, 208-230/460 V, FLA: 1.96/0.98 & 2.24/1.12, 3 phase. Galvanized coils. Refrigerant: ammonia. Inlets/outlets; (2) 2 in., flange: 6 in. center to center: 4-1/2 in. with (4) holes. For quick freezing. Overall dimensions: 95 in. L x 43 in. W x 42 in. H.

