

1999 Dual Vertical Lift Conveyor With Hopper

Mfg: Finish Food Processing Equipment

Model:

Stock No. SSLP478.12a

Serial No.:

1999 Finish Food Processing Equipment, Dual Vertical Lift Conveyor With Hopper. Type: VEW.2X250. Order: 1652. Stainless steel body. Hopper dimensions: 76 in. L x 45-3/4 in. W x 21-1/2 in. H. Bottom hopper opening: 21-1/2 in. L x 6-1/2 in. W. Belt dimensions: 9-3/4 in. W x 87-1/2 in. H. Belt clearance: 9-3/4 in. L x 5-1/2 in. W. Electrical: 460 V, 60 Hz, 3 phase. (2) Vector motors, 220-240/380-415 & 240-266/415-460 V, 3.05/1.75 & 2.75/1.59 amps, 50 & 60 Hz. Final rpm on the gear drive is 67 rpm. Drive pulley is 6 in. Feet per minute on the conveyor is 105 ft. per minute. Belt cleat height is 3 in. (2) Doors on each side. (2) Air operated top chute doors: 10 in. W x 30 in. H. Outlet: 2-1/2 in. threaded male with valve. Overall dimensions: 110 in. L x 50 in. W x 11 ft. 3 in. H.



