

## R & D Machine Heated Drum Unloader

Mfg: R & D Machine

Model:

Stock No: SSND281.15

Serial No: 04/05-3344

R & D Machine Heated Drum Unloader. S/N: 04/05-3344. (1) Thomsen centrifugal pump with a Baldor motor: Model no. 50321-KA—S, serial no. 3A47444. Motor specs: ½ hp, 1725 rpm, 115/230 v, 7.4/3.7 a, 60 Hz, 1 phase. (1) Wilden 316 stainless steel, model 4 diaphragm pump, used for unloading. (1) Dayton motor: ½ hp, 1725 rpm, 115/208-230 v, 8.2/4.0-4.1 a, 60 Hz, 1 phase. Motor has a Boston Gear drive: .470 input hp, 557 output torque, 33.99 ratio. (1) Dayton motor: ¾ hp, 1725 rpm, 115/208-230 v, 9.2/4.7-4.6 a, 60 hz, 1 phase. Motor has a Boston Gear drive: 1.15 input hp, 1457 output torque, and 36.29 ratio. Inlets/outlets: (1) 2 in. ACME, (2) 1-1/2 in. ports, (1) 1 in. FNPT. Overall dimensions: 4 ft. ¼ in. L x 3 ft. 8 in. W x 6 ft. 7 in. H.













