

Ogden Mobile Filter Press - 12 in.

Mfg: Ogden

Model:

Stock No: TAFM036.2

Serial No:

Ogden mobile filter press. Frame is equipped with (9) 12 in. dia. filter plates and (10) dividers, a mixing tank with flip open lid and float control. Plates are closed by turning a manual vise. (4) Casters allow for easy positioning. Filtering area: 7 sq. ft. Mixing tank capacity is 26 gallon, has a 18 in. dia. mixing propeller. Baldor Electric motor, 1/4 hp, 1725 rpm, 115/208-230 V, 5/2.6-2.5 amps, 60 Hz, single phase. Gear ratio: 50. Final rpm: 34.5 (Mixer). Baldor Electric motor, 1725 rpm, 115/208-230 V, 2.8/7.0-6.4 amps, 60 Hz, single phase. Driver pulley: 3 in. dia. Driven pulley: 4 in. dia. Ratio: 1.33. Final rpm: 1296 (product pump). Inlets: (1) 9-5/8 in. dia. open top (mixer tank), (2) 1 in. hose adapter fitting. outlets: (1) 1 in. dia. hose adapter fitting. Overall dimensions: 8 ft. L x 2 ft. 11 in. W x 4 ft. 11 in. H.





