

Worthington Centrifugal Pump

Mfg: Worthington

Model: UH52135

Stock No. THHS008.

Serial No. 052753-99

Worthington Centrifugal Pump. Model: UH52135. S/N: 052753-99. Used in: Boiler Feed, Catalytic Cracking, Crude Handling and Treatment, Decoking, Distillation, Gas-to-Liquids, Gas Treatment, Hydro raking, Hydrotreating, LNG, Logistics and Tank Farm, NGL, OEM, Utilities, Water Handling and Treatment. TE Motor, 15 hp, 1765 rpm, 230/460 V, 35.9/17.9 amps, 60 Hz, 3 phase. Inlets: 5 in. inlet port w/ 10 in. flange and (8) 1/2 in. thru-holes. Outlets: (1) 4 in. outlet port with a 9 in. flange and (8) 1/2 in. thru-holes. (1) 1/2 in. dia. NPT (male) valve. Overall dimensions: 51 in. L x 27 in. W x 28 in. H.

