

**S.A. Armstrong LTD. Centrifugal Pump**

**Mfg: S.A. Armstrong LTD.**

**Model: H67BF**

**Stock No: TMCB279B**

**Serial No: 8309**

Armstrong Centrifugal Pump. Model: H67BF. S/N: 8309. Baldor Electric motor: 1 Hp, 1725 Rpm, 208-230/460 V, 3.7-3.4/1.7 A, 60 Hz, 3 Phase. Inlet/outlet: (2) 2 in. dia. inner flanges, with (4) 1/2 in. dia. mounting holes, 3 in. adjacent, 4 in. opposite. Overall dimensions: 1 ft. 10 in. L x 1 ft. 3 in. W x 1 ft. H.



