

1990 Fogg F-Series 18-Head Filler

Mfg: Fogg

Model: FG-185

Stock No. WHSD001.100

Serial No. 510-74-1-92

1990 Fogg F-Series 18-Head Filler. Model: FG-185. S/N: 510-74-1-92. Container height dimensions: 4 to 12 in. Container size dimensions: 2 to 6-1/2 in. (round or square). Bottle fill level (from top of bottle): 1/4 to 3 in. Approximate filling speeds for gallon, 1/2-gallon, and quart of milk: 58, 100, 100 cpm. Approximate filling speeds for gallon, 1/2-gallon, and quart of juice: 65, 100, 100 cpm. Approximate filling speeds for gallon, 1/2-gallon, and quart of water: 75, 100, 100 cpm. Infeed tank capacity: 80 gal. Number of capping heads: 5. Air supply: 50-150 psi (plant supply), 20 psi (air regulator setting). Standard features: stainless base with 2 vertical posts, universal capping turret, Fogg/Ladish air float with 2 in. valve, DC Vari-Speed drive, electrical box and controls, conveyor that accepts 3-1/4 in. or 4-1/2 in. wide chain, 35 in. to 37 in. conveyor height, and Fogg Ventra-Flow rubber diaphragm air lock valves. Overall dimensions: 90 in. L x 75 in. W x 82 in. H.













