

## Cleaver Brooks CB Packaged Firetube Boiler- 200 HP

Mfg: Cleaver Brooks

Model: CB655-200

Stock No. 300.200

Serial No. L-28567

Cleaver Brooks CB Packaged Firetube Boiler- 200 HP. Model: CB655-200, S/N: L-28567. UL Inspection No: J50247. Steam pressure: 150 psi. Natural gas burner or #2 oil. Oil capacity: 56 gph. New low water and steam pressure controls. Includes water makeup system and pumps, new skin and paint, very low scale, in good operating condition. Skid mounted and set up to run outside. U.S. Motor, 10 hp, 3000/3600 rpm, 208-220/440 V, 28.6-27/13.5 amps, 50/60 Hz, 3 phase. Overall dimensions: 20 ft. 2 in. L x 85 in. W x 100 in. H. G&L Vertical Pump, Cat. No: 2SVBK9, (2) 1 in. dia. inlets/outlets. Baldor Industrial Motor, 3 hp, 3450 rpm, 230/460 V, 7.6/3.8 amps, 60 Hz, 3 phase. Viking Positive Displacement Pump, Model: GX-1 54, S/N: 0556938, (2) 1 in. dia. FPT inlet/outlet. Master Gearmotor, 1/4 hp, 1140/950 rpm, 230/190 rpm (final), 208-220/440 V, 1.3/0.65 amps, 60/50 Hz, 3 phase. (2) ITT Hydramotor Valves.

















