

Double Barrel Paddle Blender 70 Cubic Feet

Mfg:

Model:

Stock No. CJR1825

Serial No.

Double Barrel Paddle Blender-70 cu. ft. Stainless steel, drive shaft pulleys 17 in. diameter with chain and pulley covers. Has 2 lids dimensions 43 in. L x 21 in. W. With manholes on top. US Electric motor. S/N P830LT-2777. 1 hp, 1,745 rpm, 230/460 V, 3.6/1.8 amp, 60 Hz. Variable speed drive. S/N E74015223R021F. Frame 6, type VAM, 2.0 max hp at 1,750 rpm, max torque 54. (2) Barrel dimensions 60 in. L x 36 in. Diameter. (2) Shaft is 1-3/4 in. diameter. Compartments are connected by a 3 way valve. Overall dimensions 84 in. L x 74 in. W x 74 in. H.



