



# PACT90S

## PACKAGED AIR-COOLED 10 HP SINGLE CIRCUIT SCROLL WITH TANK

### DIMENSIONAL DRAWINGS

The drawings show the following dimensions and features:

- Top View:** Overall width is 34", overall height is 67". Two 80" x 80" fan zones are shown. A control panel is located at the bottom center with a 34" width and 81" height.
- Left Profile:** Shows the side of the unit with a 10" top section, 1/4" F-NPT chilled fluid inlet, and three louvered access panels. Mounting holes and lifting holes are indicated.
- Front View:** Shows the front of the unit with a 34" width and 67" height. It includes a micro-processor, control panel access door, access panel, and 1/4" F-NPT chilled fluid outlet. Electrical connections (4) are also shown.

LENGTH	WIDTH	HEIGHT	WEIGHT	TANK CAPACITY	FLUID CONNECTIONS
34"	85"	67"	1250 LBS	90 GAL.	1 1/4" FPT

### PRODUCT PERFORMANCE INFORMATION

REFRIGERANT	COMPRESSOR OPER. SUCTION TEMP. RANGE	LFT °F	80°F AMB		90°F AMB		95°F AMB		100°F AMB		105°F AMB	
			TONS	EER	TONS	EER	TONS	EER	TONS	EER	TONS	EER
R407C	25°F to 55°F	40	7.6	10.2	7.1	8.8	6.9	8.2	6.7	7.5	6.5	6.9
		50	9.4	12.1	8.9	10.5	8.6	9.7	8.3	9.0	8.1	8.3
		60	11.4	14.0	10.8	12.2	10.5	11.4	10.2	10.6	9.9	9.8
		70	13.6	15.9	12.9	14.0	12.6	13.0	12.3	12.1	11.9	11.3
R404A	-10°F to 45°F	5	4.3	5.8	3.9	4.8	3.7	4.3	3.4	3.9	3.2	3.5
		15	5.3	7.0	4.8	5.8	4.6	5.2	4.3	4.7	4.1	4.3
		30	7.2	8.8	6.6	7.4	6.2	6.7	5.9	6.1	5.6	5.5
		45	9.3	10.6	8.4	8.9	8.0	8.2	7.6	7.5	7.2	6.8
		60	11.6	12.4	10.6	10.5	10.1	9.7	9.5	8.8	9.1	8.1

**DRAKE REFRIGERATION INC**  
 2900 SAMUEL DRIVE  
 BENSALEM, PA 19020  
 (888) 289-7299  
[www.drakechillers.com](http://www.drakechillers.com)

\*ALL INFORMATION *FOR REFERENCE ONLY*



# PACT90S

## PACKAGED AIR-COOLED 10 HP SINGLE CIRCUIT SCROLL WITH TANK

STANDARD FEATURES	
FEATURE	BENEFIT
Listings	ETL 3046941, UL STD 1995, CAN/CSA STD, C22.2 No. 236
Micro Control Systems Controller	Open source, microprocessor built to operate in the HVAC/R industry
Controls	BMS, BAS communications, remote access, monitoring services
Stainless Steel Brazed Plate Evaporator	Corrosion resistant, fully insulated and selected upon requirements
Copeland Scroll Compressor	Industry leader, long lasting compressor
Compressor Crankcase Heater	Prevents compressor damage caused by cold refrigerant on startup
Suction Accumulator	Protects the compressor from damage caused by liquid flood back by preventing liquid from entering the compressor
Water Flow Switch	Protects against process fluid freezing caused by pump failure
Hot Gas Bypass	Aids in the prevention of evaporator freeze ups and capacity control
Copper Tube/Aluminum Fin Condenser	Rust resistant and high CFM
Painted Galvanized Steel Metal Cabinet	Sturdy, corrosion resistance, professional appearance
Insulated Process Fluid Lines	Maximum thermal efficiency
Factory Tested	Ensures the unit meets the customer's performance designed criteria and arrives in working order
Full Refrigerant Charge	Hassle free and more efficient installation
Stainless Steel Storage Tank	Closed cell insulation for increase temperature control with reliable, corrosion resistant, stainless steel recirculation pump
NEMA 3R Rated Electrical	Indoor/outdoor use
Phase Monitors	Electrical protection for compressors

AVAILABLE OPTIONS	
OPTIONS	AVAILABLE
Extended Warranty	4 year extended compressor warranty
Electrical	Compressor fusing, disconnects, circuit breakers and more
Stainless Steel Pumps	1/3 HP to 25 HP on board pumps in multiple configurations & options
Fluid Piping Upgrades	Flow meters, pressure gauges, low flow bypass valves, and more
Coastal Protection/Hazardous Environments	Heresite coating, "Gold" and Copper condenser coils
Low Ambient Protection	EC fan for temperature down to +10°F, Head pressure control for temperatures down to -20°F, Heated receivers for temperature down to -40°F
Other	Casters, service outlets, city water add-ons, heaters, etc.
<i>More options and customization available, contact factory for information: (888) 289 - 7299</i>	

## AVAILABLE MODEL NUMBER VOLTAGE REFERENCE

T3 (208-230/3/60) --- T4 (460/3/60) --- T5 (575/3/60)

PRODUCT INFORMATION											
MODELS AVAILABLE	COMPRESSOR			FAN MOTOR		RLA EA	LRA EA	MCA	MOP	EVAP. PUMP EA	
	MODEL	QTY	HP	QTY	FLA EA						
R407C R404A											
PACT90S3-T3-Z	ZB76KCE	1	10	2	3.3	41.4	239	70	105	10	
PACT90S3-T4-Z					1.6	19.2	125	30	45	2.8	
PACT90S3-T5-Z					1.72	13.8	80	25	35	1.8	
PACT90S6-T3-Z	ZB76KCE	1	10	2	3.3	41.4	239	70	105	10	
PACT90S6-T4-Z					1.6	20	125	35	50	2.8	
PACT90S6-T5-Z					1.72	13.2	80	25	30	1.8	

**DRAKE REFRIGERATION INC**  
 2900 SAMUEL DRIVE  
 BENSLEM, PA 19020  
 (888) 289-7299  
[www.drakechillers.com](http://www.drakechillers.com)

\*ALL INFORMATION **FOR REFERENCE ONLY**