

Baldor High Efficiency Electrical Motor – 200 HP

Mfg: Baldor

Model: M2562T-4

Stock No: KWBF503C

Serial No: 18F022X037H1

Baldor High Efficiency Electrical Motor – 200 HP. Catalog no.: M2562T-4. Spec. no.: 18F022X037H1. Motor specifications: 3560 rpm, 460 V, 218 amps, 60 Hz, 3 phase. Frame: 444TS. Insulation class: B. Nema design: B. Code: G. Shaft diameter: 2 .375 in. Unit weight: 1214 lbs. Overall dimensions: 3 ft. 2 in. L x 2 ft. 9 in. W x 2 ft. 2 in. H.



