

Model 90 Flake Ice Maker

Built for industrial use with high quality, heavy-duty parts, all North Star flake ice makers are constructed to be dependable and durable. The Model 90 ice maker is available in three stainless steel configurations – the Elite, Plus and Standard – for use in all types of food processing, or carbon steel, used in non-food related industries such as concrete cooling. All of these configurations produce superior, sub-cooled flake ice for industrial applications.

	D (*)
Feature	Benefit
North Star's lifetime evaporator warranty	The best warranty in the business.
Makes sub-cooled flake ice	 Superior ice for most industrial applications the greatest surface area coverage for faster, more efficient cooling.
Stainless steel components incorporated in the design (varies depending on model)	 The smart choice for food safety and sanitation, will not corrode, low maintenance requirements.
Makes ice from fresh water or salt water	 Used worldwide in seafood processing, meat and poultry processing, concrete cooling and other industries
Solid stainless steel freezing surface Elite, Plus & Standard models	 Long-lasting, durable and easy to clean. Will not chip, flake, pit or corrode like chrome-plated freezing surfaces.
Solid carbon steel freezing surface	 Also will not chip, flake or pit and corrosion-resistant while kept below freezing, or with minimal care.
Double-walled, stationary evaporator design	No refrigerant seals to leak.
Constructed to ASME and PED codes	Meets international safety requirements for pressure vessels.
Operates continuously with no defrost cycle	All energy goes to making ice.
High R-Value polyurethane insulation and reinforced fiberglass exterior	Energy efficient and durable.
North Star designed drip shield	Complete separation of water and ice. No water is wasted.
Simple installation and operation	Easy to use with minimal mainten- ance requirements.






Model 90 Flake Ice Maker

Ice Maker Specifications

High Capacity with a Small Footprint

Refrigerant Control: RFS (Refrigerant Float Switch) (Preferred) or Sporlan Levelmaster. Forced recirculation models also available

1/2" MPT Net Weight: 9,480 lbs (4300 kg) Oil Drain Line: Volume: 645 ft³ (18.3 m³) Water Line: **Drive Motor:** 1 1/2 HP Tank Inlet 1/2" FPT Pump Motor: 1/2 HP Tank Drain 1 1/4" FPT Pump Outlet **Suction Line:** 6" Sch 40 1 1/4" FPT 2" Sch 80 **Liquid Line:** Flow Control Valve Inlet 1 1/2" FPT



				/////						
Refrigerant Capacity at 70°F (21°C) Volume 17.1 Cubic Feet (.49 Cubic Meters)				Refrigeration Requirement Tons of Refrigeration Per Ton of Ice						
Freon R-134a	1,400 lbs (635 kg)	Freon R-404a	1,350 lbs (612 kg)	Water Temp. °F Tons of Ref (UST)	40 1.20	50 1.25	60 1.30	70 1.40	80 1.50	
Freon R-22	1,300 lbs (590 kg)	Ammonia R-717	650 lbs (295 kg)	Water Temp. °C kW of Ref (MT)	5.0 4.67	10 4.84	15.5 5.02	21 5.44	27 5.91	

Flake Ice Capacities in US Tons (Metric Tons)

Evap. Temp F	0	-5	-10	-15	-20	-25	-30	-35
- C	-18	-21	-23.5	-26	-29	-32	-34.5	-37
Stainless Steel Models 1.5mm Ice Thickness 2.0mm Ice Thickness	24.1 (22.0) 20.6 (18.9)	27.3 (25.3) 23.4 (21.6)	30.9 (28.2) 26.2 (24.0)	34.4 (31.0) 29.2 (26.4)	37.5 (34.1) 32.2 (29.3)	40.3 (37.0) 35.1 (32.1)	42.5 (38.5) 37.4 (33.9)	
Carbon Steel Models 1.5mm Ice Thickness 2.0mm Ice Thickness	29.3 (26.9)	34.3 (31.8)	39.3 (35.9)	44.1 (39.8)	48.9 (44.5)	53.0 (48.5)	56.1 (50.5)	58.3 (52.8)
	23.9 (22.0)	28.3 (26.3)	32.6 (29.8)	36.9 (33.4)	41.2 (37.5)	44.9 (41.2)	48.0 (43.6)	50.3 (45.5)

Above capacities based on 60°F (15.5°C) make-up water and oil-free ammonia refrigerant. For different operating conditions including halocarbon refrigeration, please visit the North Star Website and use our Ice Maker Selector Tool at: www.northstarice.com.

North Star Ice Equipment Corporation

8151 Occidental Avenue South P.O. Box 80227 Seattle, WA 98108 USA Tel: 206-763-7300

Toll-free in USA: 1-800-321-1381

Fax: 206-763-7323 Email: info@northstarice.com



www.northstarice.com