

## 1999 Bryan Boiler Feedwater Deaerator

Mfg: Bryan

Model: DSH-150-25-5-3

Stock No. pHDHP142.25

Serial No. 84712

1999 Bryan Boiler Feedwater Deaerator. Model: DSH-150-25-5-3, S/N: 84712. Feedwater deaerator maximizes boiler efficiency by pre-heating boiler feedwater. Complete with Allen-Bradley control box and 6-1/2 in. dia. x 57-1/2 in. L water header. Oval manway dimensions: 16 in. L x 12 in. W. (3) Grundfos Pumps: Model: C 41006070E P1 9931, Type: CR4-100 11-GA-AUUE, 22 gpm at 360 ft. of head, 3450 rpm, 300 psi (max), 250 F (max). (3) Baldor Industrial Motors: 5 hp, 3450 rpm, 208-230/460 V, 13.2-12/6 amps, 60 Hz, 3 phase. Inlets/outlets: (1) 3 in. dia. feedwater inlet, (1) 6 in. dia. inlet with an 11 in. dia. flange and (8) 3/4 in. dia. attachment holes, (1) 3 in. dia. outlet to boiler. Overall dimensions: 10 ft. 10 in. L x 60 in. W x 9 ft. 10 in. H.

(3) ITT McDonnell low water cut-off valves, MAWP: 50 psi.

