




XLC130—770-2





XLC130—XLC250

XLC285—XLC385



XLC410-2—XLC500-2

XLC570-2—XLC770-2



XLC Model ¹	NH ₃		Fan Mtr HP	Spray Water GPM	Pump Mtr HP	REMOTE SUMP			DIMENSIONS				Refrig. Charge NH ₃ lbs. ⁵	WEIGHTS		
	Tons ²	CFM				Water In ³	Sump Drain ³	Gal. Req'd ⁴	Height H	Ctrs B	Width W	Base C		Unit Shipping ⁶	Unit Operating ⁷	Heaviest Section
155	109.9	23700	7.5	180	1	3*	4**	95	113.625	44.25	102.5	60.0	196	7740	9040	6460
160	113.5	26400	10	180	1	3*	4**	95	106.875	37.5	102.5	60.0	170	7210	8630	5930
165	117	26000	10	180	1	3*	4**	95	113.625	44.25	102.5	60.0	205	7770	9060	6490
170	120.6	29400	15	180	1	3*	4**	95	106.875	37.5	102.5	60.0	178	7260	8670	5980
185	131.2	29400	15	180	1	3*	4**	95	113.625	44.25	102.5	60.0	224	7810	9090	6530
195	138.3	36800	15	240	1.5	3*	5**	130	99.625	30.25	125.5	83.0	190	7700	9480	6420
205	145.5	40500	20	240	1.5	3*	5**	130	99.625	30.25	125.5	83.0	197	7740	9520	6460
220	156	36600	15	240	1.5	3*	5**	130	106.875	37.5	125.5	83.0	238	8910	10860	7630
230	163.1	40200	20	240	1.5	3*	5**	130	106.875	37.5	125.5	83.0	246	8950	10900	7670
235	166.7	36400	15	240	1.5	3*	5**	130	113.625	44.25	125.5	83.0	285	9960	12090	8680
250	177.3	40050	20	240	1.5	3*	5**	130	113.625	44.25	125.5	83.0	299	10000	12130	8720
285	202.1	53400	20	370	3	3*	6**	205	99.625	30.25	125.5	83.0	280	11340	14110	9165
300	212.8	57500	25	370	3	3*	6**	205	99.625	30.25	125.5	83.0	291	11390	14160	9215
310	219.8	61100	30	370	3	3*	6**	205	99.625	30.25	125.5	83.0	298	11430	14200	9255
340	241.1	57300	25	370	3	3*	6**	205	106.875	37.5	125.5	83.0	364	13130	16170	10955
350	248.2	60900	30	370	3	3*	6**	205	106.875	37.5	125.5	83.0	372	13170	16210	10995
365	258.9	57000	25	370	3	3*	6**	205	113.625	44.25	125.5	83.0	437	14690	18000	12515
385	273	60500	30	370	3	3*	6**	205	113.625	44.25	125.5	83.0	454	14740	18050	12565
410-2	290.8	81000	(2)20	480	(2)1.5	(2)3*	(2)5**	260	99.625	30.25	125.5	83.0	394	15480	19050	(2)6465
440-2	312	73200	(2)15	480	(2)1.5	(2)3*	(2)5**	260	106.875	37.5	125.5	83.0	476	17830	21750	(2)7640
460-2	326.2	80000	(2)20	480	(2)1.5	(2)3*	(2)5**	260	106.875	37.5	125.5	83.0	492	17910	21830	(2)7680
470-2	333.3	72800	(2)15	480	(2)1.5	(2)3*	(2)5**	260	113.625	44.25	125.5	83.0	570	19910	24170	(2)8675
500-2	354.6	80100	(2)20	480	(2)1.5	(2)3*	(2)5**	260	113.625	44.25	125.5	83.0	598	19980	24250	(2)8715
570-2	404.2	106800	(2)20	740	(2)3	(2)3*	(2)6**	410	99.625	30.25	125.5	83.0	560	22670	28210	(2)9160
600-2	425.5	115000	(2)25	740	(2)3	(2)3*	(2)6**	410	99.625	30.25	125.5	83.0	582	22770	28320	(2)9210
620-2	439.7	122200	(2)30	740	(2)3	(2)3*	(2)6**	410	99.625	30.25	125.5	83.0	596	22860	28410	(2)9250
680-2	482.3	114600	(2)25	740	(2)3	(2)3*	(2)6**	410	106.875	37.5	125.5	83.0	728	26260	32340	(2)10955
700-2	496.4	121800	(2)30	740	(2)3	(2)3*	(2)6**	410	106.875	37.5	125.5	83.0	744	26340	32430	(2)10995
730-2	517.7	114000	(2)25	740	(2)3	(2)3*	(2)6**	410	113.625	44.25	125.5	83.0	874	29380	36010	(2)12520
770-2	546.1	121000	(2)30	740	(2)3	(2)3*	(2)6**	410	113.625	44.25	125.5	83.0	908	29470	36100	(2)12570

*Male Pipe Thread

**Female Pipe Thread