



INCLUDED OPTIONS: .080" TUBE COIL; FAN LEVEL HANDRAILS AND LADDER; JIB BOOM ASSIST; REST PLATFORM AND SIDE EXIT CAGE.

STANDARD UNIT DATA:
 CASING: GALVANIZED STEEL
 REMOTE: 1050 GPM @ 2.0 PSI
 FAN MOTOR: (1) 30 HP TEAD 1800 RPM
 460-3-50 226T FRAME
 FOUNDATION LAYOUT: B-5290005

PERFORMANCE DATA:
 5295 MBH THR @ 75F WB
 90°F COND
 R-717
 0" ESP
 DESIGN PRESSURE: 300 PSI

		FRICK SO# 269324		CUSTOMER PO# VO TEETER	
		IMECO SO# 22067		SCALE: NONE	
		DATE: 9/15/99		NO. REQS: 3	
		DRAWN BY: J.BOELENS		CHKD BY:	
		APVD BY:		CUSTOMER	
		FRICK COMPANY		REPUBLIC REFGN.	
		MODEL: SIDC 653		DRAWING NO. 5100029	
		EVAP. CONDENSER		1/1	

DO NOT SCALE PRINT
 VERT. TO DIMENSIONS
 ALL DIMENSIONS
 ARE OUTSIDE UNLESS
 OTHERWISE SPECIFIED