




VC2 Axial Fan

Do not use for construction. Refer to factory certified dimensions.
This brochure includes data current at time of publication, which should be reconfirmed at the time of purchase.



Model Number	R-717 Tons	Approx. Shpg. Weight (lbs)	Approx. Oper. Weight (lbs)	Heaviest Section (Coil) (lbs)	CFM	Motor HP (0" ESP)	GPM	Pump Motor HP	R-717 Oper. Charge (lbs)	Internal Coil Volume (ft ³)	REMOTE SUMP			F	H
											Drain Size	Approx. Oper. Weight	Gal Req.		
VC2-319	226	15,240	24,590	10,300	54,300	7.5	585	5	445	55	8	19,550	480	33 1/4	163 1/2
VC2-342	243	15,290	24,640	10,300	59,750	10	585	5	445	55	8	19,600	480	33 1/4	163 1/2
VC2-377	267	15,340	24,690	10,300	68,400	15	585	5	445	55	8	19,650	480	33 1/4	163 1/2
VC2-420	298	17,410	26,970	12,370	68,400	15	585	5	550	68	8	21,930	480	42 1/2	172 3/4
VC2-451	320	17,420	26,980	12,370	73,100	20	585	5	550	68	8	21,940	480	42 1/2	172 3/4
VC2-471	334	19,450	29,010	14,400	71,400	20	585	5	675	81	8	23,970	480	51 3/4	182
VC2-491	348	19,470	29,030	14,400	76,950	25	585	5	675	81	8	23,990	480	51 3/4	182
VC2-513	364	19,490	29,050	14,400	81,750	30	585	5	675	81	8	24,010	480	51 3/4	182
VC2-541	384	20,870	30,510	15,780	81,500	30	585	5	750	91	8	25,470	480	51 3/4	182
VC2-580	411	21,060	30,700	15,780	89,700	40	585	5	750	91	8	25,660	480	51 3/4	182
VC2-585	415	22,740	33,445	18,205	77,040	30	585	5	875	106	8	28,405	480	61	194 1/4
VC2-626	444	22,795	33,500	18,205	85,200	40	585	5	875	106	8	28,460	480	61	194 1/4
VC2-526	373	22,220	36,430	15,170	89,700	10 & 5	835	5	665	82	10	29,050	670	33 1/4	163 1/2
VC2-581	412	22,330	36,540	15,170	102,650	15 & 7.5	835	5	665	82	10	29,160	670	33 1/4	163 1/2
VC2-623	442	22,350	36,560	15,170	113,000	20 & 10	835	5	665	82	10	29,180	670	33 1/4	163 1/2
VC2-642	455	25,450	39,990	18,290	99,600	15 & 7.5	835	5	825	101	10	32,610	670	42 1/2	172 3/4
VC2-688	488	25,470	40,010	18,290	109,650	20 & 10	835	5	825	101	10	32,630	670	42 1/2	172 3/4
VC2-711	504	28,580	43,450	21,400	107,150	20 & 10	835	5	990	121	10	36,070	670	51 3/4	182
VC2-752	533	28,680	43,550	21,400	115,400	25 & 15	835	5	990	121	10	36,170	670	51 3/4	182
VC2-785	557	28,700	43,570	21,400	122,650	30 & 15	835	5	990	121	10	36,190	670	51 3/4	182
VC2-827	587	30,780	45,760	23,480	122,200	30 & 15	835	5	1,100	135	10	38,380	670	51 3/4	182
VC2-887	629	30,980	45,960	23,480	134,500	40 & 20	835	5	1,100	135	10	38,580	670	51 3/4	182
VC2-895	635	33,655	49,895	27,160	115,000	30 & 15	900	7.5	1,290	158	10	42,515	670	61	194 1/4
VC2-957	679	33,765	50,005	27,160	126,080	40 & 20	900	7.5	1,290	158	10	42,625	670	61	194 1/4

See previous page for notes.